

F256A

Moisture Regain Oven

Moisture Regain Oven.To determine the moisture content and regain percentage of textile materials. Drying is performed by circulation of warm air electrically heated regulated by and electronic temperature controller. The material to be tested is dried within a metal container suspended from and electronic balance. Two successive weights of the same value determine the point which moisture content can be calculated.

Specifications	F256A
Weight	1 kg
Dimensions	100 x 50 x 200 mm (WxDxH)
Standards	No Standards



F256A

- To determine the moisture content and regain percentage of textile materials.
- The material to be tested is dried within a metal container suspended from and electronic balance.